

Nova Kool Mfg. ULC

Replacing a RFU8000 with an RFU9000:

The RFU9000 can often be used as a replacement for the RFU8000, however be sure to measure the cutout space to ensure the new unit will fit.

The outside flange dimensions are the same on both units, but RFU9000 has a deeper cut-out. The below offers a guide on the differences.

Please call Nova Kool if you require further solution options. 604-523-6515

RFU9000:

Outside flange dimensions:

53 3/8H x 24 ¾ W

Cut out:

52 7/8 x 23 ¼ W x 22 3/4D





RFU8000:

Outside flange dimensions:

53 3/8H x 24 ¾ W

Cut out:

Can fit in a cut-out from

50 ½ x 20 ¼ W x 22 1/2D

То

52 7/8 x 23 ¼ W x 22 1/2D



